

20mm Dia. Left-Handed VIS-Coated Glass Circular Polarizer (CP42HE)



Stock #19-934 3-4 DAYS

- 1 + **€58,00**

ADD TO CART

Qty 1-9
€58,00

Qty 10+
€53,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Coating: VIS AR Coated
Diameter (mm): 20.00
Substrate: ☐ Polymer Film CP42HE Laminated Between Glass

Operating Temperature (°C): -40 to +80
Thickness (mm): 2.00 ±0.10
Transmission (%): 45 ±2
Type: Left-Handed Circular Polarizer
Dimensional Tolerance (mm): ±0.20
Construction: Laminated Glass Polarizing Film
Coating Specification: R _{avg} <0.5% @ 425 - 700nm
Wavelength Range (nm): 425 - 700
Polarization Efficiency (%): >99.90

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant