

**TECHSPEC®** 20mm NIR, 70R/30T, Non-Polarizing Cube Beamsplitter



Stock #13-439 3-4 DAYS

⊖ 1 ⊕ **€239,00**

ADD TO CART

|         |
|---------|
| Qty 1-5 |
| €239,00 |

|         |
|---------|
| Qty 6+  |
| €189,00 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Beam Deviation (arcmin):**  
≤2

**Bevel:**  
Protective bevel as needed

**Clear Aperture (%):**  
>90

|                                                                 |
|-----------------------------------------------------------------|
| Coating:<br>NIR                                                 |
| Coating Specification:<br>R <sub>avg</sub> <0.5% @ 720 - 1080nm |
| Construction:<br>Cube                                           |
| Dimensions (mm):<br>20.0 x 20.0 x 20.0 ±0.1                     |
| Reflection/Transmission Ratio (R/T):<br>70/30                   |
| Substrate: <input type="checkbox"/><br>N-BK7                    |
| Surface Flatness (P-V):<br>λ/8                                  |
| Surface Quality:<br>40-20                                       |
| Type:<br>Non-Polarizing Beamsplitter                            |
| Wavelength Range (nm):<br>720 - 1080                            |
| Ts-Tp :<br><6%                                                  |
| Absolute Transmission (%):<br>27 ±10                            |
| Average Transmission (%):<br>27 ±5                              |
| Power (fringes) @ 632.8nm:<br>1.25                              |
| Irregularity (fringes) @ 632.8nm:<br>0.25                       |

Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS:<br><a href="#">Compliant</a>                  |
| Certificate of Conformance:<br><a href="#">View</a> |