

TECHSPEC® 20mm NIR, Lateral Displacement Non-Polarized Beamsplitter



Lateral Displacement Beamsplitters

Stock **#47-541** 3-4 DAYS



1



€705,00

ADD TO CART

Qty 1-5

€705,00

Qty 6+

€564,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle Tolerance (arcsec):
±5

Beam Separation (mm):
20.00

Clear Aperture (%):
80.00

Coating Specification: R_{avg} <0.5% @ 720 - 1080nm
Construction: Prism
Dimensional Tolerance (mm): ±0.1
Extinction Ratio: T_p - T_s <6%
P-Polarization Transmission (%): 45.00
Parallelism (arcmin): <2
S-Polarization Reflection (%): 45.00
Substrate: N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Type of Optics: Non-Polarizing
Wavelength Range (nm): 720 - 1080

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View