

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

200mm Square, 45° AOI, Hot Mirror



Hot Mirrors

Stock #62-628 3-4 DAYS

1 €42,00

ADD TO CART

Qty 1-9

€42,00

Qty 10+

€36,80

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
45.00

Coating:
Hot Mirror, 45°

Substrate: BOROFLOAT®

Reflection (%): >90, 750 - 1125nm
Dimensions (mm): 20.0 x 20.0
Surface Quality: 80-50
Thickness (mm): 1.10
Transmission (%): >85, 425 - 675nm
Type: Dichroic Filter
Dimensional Tolerance (mm): ±0.5
Coating Specification: Surface 1: 45° Hot Mirror Surface 2: None
Wavelength Range (nm): 425 - 1125
Surface Flatness (P-V): 4 - 6λ
Coating Type: Dielectric

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant