

TECHSPEC® 20mm, Uncoated, N-BK7 Right Angle Prism



N-BK7 Right Angle Prisms

Stock #32-334 In Stock

1 **€63,00**

ADD TO CART

Qty 1-5

€63,00

Qty 6+

€56,70

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
Uncoated

Substrate:
[N-BK7](#)

Surface Quality:

60-40

Type:
Right Angle Prism

Dimensional Tolerance (mm):
±0.1

Angle Tolerance (arcmin):
±2

Bevel:
Protective bevel as needed

Length of Hypotenuse (mm):
28.30

Length of Legs (mm):
20.00

Image Orientation:
Left-Handed

Ray Deviation (°):
90

Wavelength Range (nm):
350 - 2200

Power (fringes) @ 632.8nm:
1.25

Irregularity (fringes) @ 632.8nm:
0.50

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 219:
[Compliant](#)

Certificate of Conformance:
[View](#)
