

## 20" x 24" UV Filter Sheet



Stock #39-426 **20+ In Stock**

⊖ 1 ⊕ €29<sup>50</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€29,50 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Longpass Filter **Type:**

### Physical & Mechanical Properties

508.0 x 609.6 **Dimensions (mm):**

609.60 **Length (mm):**

20 x 24 **Dimensions (inches):**

508.00 Width (mm):

## Optical Properties

400.00 Cut-On Wavelength (nm):

Polyester Film Substrate:

Clear Color:

200 - 750 Wavelength Range (nm):

## Regulatory Compliance

Compliant Reach 191:

Compliant RoHS 2015:

View Certificate of Conformance:

## Product Details

- Virtually Transparent, Flexible Polyester Filter
  - Deep-Dyed PET Substrate to Absorb UVA, UVB, and UVC Rays
  - <10% Transmission Below 390nm
- Flexible Thin Film UV Filters block UVA, UVB, and UVC wavelengths while transmitting visible illumination. These filters are ideal for applications where ultraviolet rays have harmful effects.

## Technical Information

