

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® Z1 X 30mm Protected Aluminum, λ/4 Mirror



Stock #32-454 ☒ In Stock



1



€47,50

ADD TO CART

Qty 1-5

€47,50

Qty 6+

€38,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: ☐
[BOROFLOAT®](#)

Back Surface:
Ground

Surface Quality: 60-40
Dimensions (mm): 21.0 x 30.0
Dimensional Tolerance (mm): +0/-0.5
Coating Specification: R_{avg} >85% @400 - 700nm R_{avg} >90% @400 - 2000nm
Coating: Protected Aluminum (400-2000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 5.00 +0.5/-0
Type: Flat Mirror
Wavelength Range (μm): 0.4 - 2.0
Wavelength Range (nm): 400 - 2000
Length (mm): 30.00
Width (mm): 21.00
Damage Threshold, Reference: 0.3 J/cm² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant