

[See all 7 Products in Family](#)

## 2.15" 625nm, LED Darkfield Illuminator

See More by [Advanced Illumination](#)



Stock **#66-791** [CONTACT US](#)

-

1

+

€415<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €415,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

| Product Downloads |
|-------------------|
|-------------------|

| General       |                       |
|---------------|-----------------------|
| RL2115-660-24 | Model Number:         |
| 50,000        | LED Lifetime (hours): |
| 15.00         | Number of LEDs:       |
|               | Number of Channels:   |

|                                                                                                                     |                       |
|---------------------------------------------------------------------------------------------------------------------|-----------------------|
| 1.00                                                                                                                |                       |
| LED Illuminator                                                                                                     | Type of Illumination: |
|                                                                                                                     | Note:                 |
| Requires a 24V power supply <a href="#">#66-855</a> . European power supply <a href="#">#35-200</a> also available. |                       |
| Advanced Illumination                                                                                               | Manufacturer:         |
| Ring Light                                                                                                          | Geometry:             |
| Constant                                                                                                            | Illumination Mode:    |

Physical & Mechanical Properties

|            |                      |
|------------|----------------------|
| 19.0       | Height (mm):         |
| 19.0       | Inner Diameter (mm): |
| 55.0       | Outer Diameter (mm): |
| 6.4 - 12.7 | Field Coverage (mm): |

Optical Properties

|           |                        |
|-----------|------------------------|
| Red       | Color:                 |
| 625       | Wavelength (nm):       |
| 19 - 25.4 | Working Distance (mm): |

Electrical

|       |                                 |
|-------|---------------------------------|
| 30.00 | Maximum Trigger Frequency (Hz): |
|-------|---------------------------------|

Hardware & Interface Connectivity

|                                                                                                                                                                                                                     |               |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| Flying Leads                                                                                                                                                                                                        | Connector:    |
|                                                                                                                                                                                                                     | Power Supply: |
| Power Supply Required and Sold Separately:<br>USA: <a href="#">#66-855</a><br>Europe: <a href="#">#66-855</a><br>Japan: <a href="#">#89-513</a><br>Korea: <a href="#">#33-773</a><br>China: <a href="#">#66-855</a> |               |

Threading & Mounting

|          |                   |
|----------|-------------------|
| Standard | Mount:            |
| M3 x2    | Mounting Threads: |

Environmental & Durability Factors

|          |                             |
|----------|-----------------------------|
| 0 to +65 | Operating Temperature (°C): |
|----------|-----------------------------|

Regulatory Compliance

|                           |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">View</a>      | Certificate of Conformance: |
| <a href="#">Compliant</a> | Reach 233:                  |

Product Details

- Ideal for Visually Enhancing Surface Defects
- Useful for Front or Back Illumination
- 5" Versions Have Variable Intensity

Advanced Illumination Darkfield LED Illuminators are ideal for visually enhancing surface defects. LED intensity can be varied through the in line potentiometer. The 5" darkfield illuminator includes a mounting bracket for easy system integration.

**Note:** Required 24V power supply [#66-855](#). [Accessories for Advanced Illumination products](#) are available and sold separately.

The strobed models' flash duration is dependent on a trigger signal or potentiometer setting. The duration of the strobe can be adjusted from 30 - 300µs via a knob located in the back of the unit. Trigger input signal is CMOS/TTL compatible. The maximum trigger frequency is 30Hz.



Ring Light Configuration

**DOWNLOAD  
NOW**

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to ¼-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



Application Note

Illumination Mounts for Machine Vision Applications  
[Read](#)



Video

Assembly of 3D Printed Mounts for Common Illumination Geometries  
[Watch](#)