

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 22 X 22mm Protected Gold, $\lambda/4$ Mirror



Stock #32-433 3-4 DAYS

1 €72,50

ADD TO CART

Qty 1-5

€72,50

Qty 6+

€58,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
 $\lambda/4$

Substrate: 
BOROFLOAT®

Back Surface:
Ground

Surface Quality: 60-40
Dimensions (mm): 22.0 x 22.0
Dimensional Tolerance (mm): +0/-0.5
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 5.00 +0.5/-0
Type: Flat Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Length (mm): 22.00
Width (mm): 22.00
Damage Threshold, Reference:  0.8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View