

14mm Max. Aperture, Iris Diaphragm



Stock **#42-123** [CONTACT US](#)

-

1

+

€66,00

ADD TO CART

Qty 1-4
€66,00

Qty 5+
€58,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
1.0

Maximum Aperture (mm):
14.0

Outer Diameter (mm):

22.0
Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 4.00
Lever Length (mm): 12.0
Number of Leaves: 10
Thickness (mm): 6.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant
