

[See all 2 Products in Family](#)

230V, with UK Cord, DC950HK Illuminator

See More by [Dolan-Jenner](#)



230V, with UK Cord, DC950HK Illuminator, #62-006

Stock **#62-006** **3 In Stock**

- 1 + €1.195⁰⁰

ADD TO CART

Volume Pricing

Qty 1-5	€1.195,00 each
Qty 6+	€1.075,50 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

150 WEKE Quartz Halogen **Type:**

0.5VDC or 8 bit digital optional **Intensity Control Option:**

Lamp Lifetime (hours):

200 - 10,000

Type of Illumination:

Fiber Optic Illuminator, Incandescent

Compatible Light Guide Adapter:

25mm Interface: **MX** (Preferred), **SX** for semi-rigid light guides or hybrid light guides

Manufacturer:

Dolan-Jenner

Illumination Mode:

Constant

Physical & Mechanical Properties

Height (inches):

4.5

Length (inches):

9.5

Weight (lbs):

11.5

Width (inches):

7.25

Construction:

Aluminum

Optical Properties

Color:

White

Electrical

Voltage (V):

230

Output Power (Lumens):

1800.00

Ripple (%):

0.4% or better

Hardware & Interface Connectivity

Power Supply:

± 0.5% or better regulation

Environmental & Durability Factors

Operating Temperature (°C):

+5 to +40

Operating Humidity:

0% to 80% non-condensing

Regulatory Compliance

Reach 174:

[Compliant](#)

Certificate of Conformance:

[View](#)


Product Details

Requires Dolan-Jenner SX Fiber Optic [Adapters](#).

- DC-Regulated Power Supply Less Than 0.5%
- Low Output Power Ripple Less Than 0.4%
- Remote Intensity Control from 0-5V DC Analog
- 200 to 10,000 Hours Lamp Life

The DC-950H is a cost effective 150W quartz halogen light source designed specifically for machine vision lighting. This light source has a compact footprint, making it a great addition to any lab or workspace. In addition to the 0 to 100% intensity control and heat absorbing filter, the basic model features less than 0.4% variation in the power output as compared to typical 2% variance in non-regulated or AC-regulated illuminators. Built-in remote interface permits precise intensity control of output power via 0-5VDC analog input or an 8 bit digital interface. Dolan-Jenner SX Fiber Optic [Adapters](#) are sold separately and required for use with a light guide.

Technical Information



Dolan-Jenner Illuminator

