

## 2.38mm Diameter, Ruby Ball Lens



Sapphire and Ruby Ball Lenses

Stock **#46-228** 3-4 DAYS

⊖ 1 ⊕ **€23,50**

ADD TO CART

Qty 1-10

€23,50

Qty 11+

€18,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
2.38

**Substrate:** ☐  
Ruby Doped Sapphire (Al<sub>2</sub>O<sub>3</sub>)

**Coating:**  
Uncoated

|                                                                          |
|--------------------------------------------------------------------------|
| <b>Type:</b><br>Ball Lens                                                |
| <b>Wavelength Range (nm):</b><br>600 - 5500                              |
| <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b><br>8.4 |
| <b>Index of Refraction n<sub>d</sub>:</b><br>1.77                        |
| <b>Melting Temperature (°C):</b><br>2053.00                              |
| <b>Porosity (%):</b><br>0.00                                             |
| <b>Specific Gravity (g/cm³):</b><br>3.98                                 |
| <b>Sphericity (µm):</b><br>0.625                                         |
| <b>Wavelength Range (µm):</b><br>0.6 - 5.5                               |
| <b>Compressive Strength (psi):</b><br>300,000                            |
| <b>Diameter Tolerance (µm):</b><br>±2.54                                 |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |