

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

24mm Diameter X 19.7mm FL, MgF₂ Coated, Aspneric Condenser Lens



Stock #15-534 [CONTACT US](#)

[Other Coating Options](#)



1



€61,00

ADD TO CART

Qty 1-10

€61,00

Qty 11+

€54,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
24.00 +0.1/-0.2

Effective Focal Length EFL (mm):
19.70

Numerical Aperture NA:
0.66

Back Focal Length BFL (mm): 11.70
Substrate: B270
Focal Length Tolerance (%): ±7
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Centering (arcmin): ≤30
Surface Quality: 80-50 (typical)
Clear Aperture CA (mm): 21.6
Edge Thickness ET (mm): 2
Center Thickness CT (mm): 10.40 ±0.2
f/#: 0.8
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 24.0
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 400 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant