

TECHSPEC® 25 x 25mm UV Enhanced Aluminum, λ/4 Mirror



Stock **#45-334** 3-4 DAYS

⊖ 1 ⊕ **€62,50**

ADD TO CART

Qty 1-5
€62,50
Qty 6+
€50,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: □
[BOROFLOAT®](#)

Back Surface:
Commercial Polish

Surface Quality: 60-40
Dimensions (mm): 25.0 x 25.0
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%) : 85
Edges: Fine Ground
Thickness (mm): 6.00 ±0.25
Type: Flat Mirror
Wavelength Range (μm): 0.25 - 0.7
Wavelength Range (nm): 250 - 700
Length (mm): 25.00
Width (mm): 25.00
Damage Threshold, Reference:  0.5 J/cm ² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant