

25 x 38mm, 70R/30T, Plate Beamsplitter



Stock #46-669 3-4 DAYS

⊖ 1 ⊕ **€55,00**

ADD TO CART

Qty 1-9
€55,00
Qty 10+
€42,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: $\lambda/4$ MgF_2 @ 550nm

Construction:
Plate

Dimensional Tolerance (mm):
±0.38

Dimensions (mm): 25.0 x 38.0
Edges: Cut
Reflection/Transmission Ratio (R/T): 70/30
Substrate: ☐ Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 3.00
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant