

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25.0mm Dia. x 175.0mm FL, MgF₂ Coated, Plano-Convex Lens



Stock #32-866 3-4 DAYS

[Other Coating Options](#)



1



€35,00

ADD TO CART

Qty 1-9

€35,00

Qty 10+

€31,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):

175.00 @587.6nm
Back Focal Length BFL (mm): 172.85
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.50 ±0.10
Edge Thickness ET (mm): 2.63
Radius R₁ (mm): 90.47
Clear Aperture CA (mm): 24
f/#: 7
Numerical Aperture NA: 0.07
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant