

**TECHSPEC® 25.0mm Dia. x -35 FL, Uncoated, Plano-Concave Lens**



TECHSPEC Uncoated Plano-Concave (PCV) Lenses



Stock **#48-680** 3-4 DAYS

[Other Coating Options](#)

− 1 + **€32,00**

ADD TO CART

|         |
|---------|
| Qty 1-9 |
| €32,00  |

|         |
|---------|
| Qty 10+ |
| €28,75  |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
25.00 +0.0/-0.025

|                                                             |
|-------------------------------------------------------------|
| <b>Effective Focal Length EFL (mm):</b><br>-35.00           |
| <b>Substrate:</b> <a href="#">N-SF11</a>                    |
| <b>f/#:</b><br>1.4                                          |
| <b>Numerical Aperture NA:</b><br>0.36                       |
| <b>Coating:</b><br>Uncoated                                 |
| <b>Type:</b><br>Plano-Concave Lens                          |
| <b>Wavelength Range (nm):</b><br>400 - 2500                 |
| <b>Back Focal Length BFL (mm):</b><br>-36.96                |
| <b>Bevel:</b><br>Protective bevel as needed                 |
| <b>Center Thickness CT (mm):</b><br>3.50                    |
| <b>Center Thickness Tolerance (mm):</b><br>±0.10            |
| <b>Centering (arcmin):</b><br><1                            |
| <b>Clear Aperture CA (mm):</b><br>24.00                     |
| <b>Edge Thickness ET (mm):</b><br>6.36                      |
| <b>Focal Length Specification Wavelength (nm):</b><br>587.6 |
| <b>Focal Length Tolerance (%):</b><br>±1                    |
| <b>Radius R<sub>1</sub> (mm):</b><br>-27.47                 |
| <b>Surface Quality:</b><br>40-20                            |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                       |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                 |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |