

TECHSPEC® 25.0/25.4mm Optic Dia., Kinematic Mount, 3-Screws



25/25.4mm Diameter Kinematic Mount, 3-Screws , #58-854



Stock **#58-854** ☐ In Stock

1 **€99,00**

ADD TO CART

Qty 1-4
€99,00
Qty 5+
€89,10
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Adjustable - Tip-Tilt

Type of Optics:
Circular

Size of Compatible Optics (mm): 25.0 - 25.4
Number of Adjustment Screws: 3
Clear Aperture CA (mm): 22.9
Travel (mm): Z-Axis: 8
Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings
Angle Tolerance (°): 0.4 per 0.25mm turn
Fine Tilt Angle (°): ±5
Fine Tip Angle (°): ±5
Sensitivity per 1° Knob Rotation (arcsec): 4
Thermal Stability (μrad): <5
Adjustment Screw Pitch (mm): 0.25
Note: Available in Quick Start Kit: #17-523
Compatible Post: M4 x0.7, 8-32
Min. Thickness of Compatible Optics (mm): 1.8
Pointing Stability (μrad): 1.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View