

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 25.4 X 25.4mm X -50mm FL, NIR Imaging Grade PCV Cylinder Lens



TECHSPEC® Beam Shaping PCV Cylinder Lenses

Stock **#35-006** [CONTACT US](#)



1



€116,00

ADD TO CART

Qty 1-5

€116,00

Qty 6+

€92,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):

-50.00

Substrate: ☐

[N-BK7](#)

f/#:

2

Numerical Aperture NA: 0.25
Coating: NIR I (600-1050nm)
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 600 - 1050
Back Focal Length BFL (mm): -52.64
Bevel: Protective bevel as needed
Center Thickness CT (mm): 4.00
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 22.86 x 22.86
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Dimensional Tolerance (mm): +0.0/-0.025
Dimensions (mm): 25.4 x 25.4
Edge Thickness ET (mm): 7.22
Radius R₁ (mm): 25.84
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <5
Power Axis Wedge (arcmin): <5
Axial Twist (arcmin): <3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant