

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #35-571 3-4 DAYS

[Other Coating Options](#)



1



€515,00

ADD TO CART

Qty 1-5

€515,00

Qty 6+

€463,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
25.40 +0.00/-0.38

Effective Focal Length EFL (mm):

177.80
Focal Length Tolerance (%) : ±1
Radius of Curvature (mm) : 177.80
Coating : Protected Gold (700-10000nm)
Coating Type : Metal
Coating Specification : R _{avg} ≥94% @ 700 - 800nm R _{avg} ≥97% @ 800 - 2,000nm R _{avg} ≥98% @ 2,000 - 12,000nm
Off-Set Angle (°) : 90
Parent Focal Length PFL (mm) : 88.9
Surface Figure, RMS : λ/4
Surface Roughness (Angstroms) : <100 RMS
Wavelength Range (nm) : 700 - 10000
Clear Aperture (%) : 90
Surface Quality : 80-50
Compatible Mounting Plates : #47-111
Substrate : Aluminum 6061-T6
Y Offset (mm) : 177.8
Reflected Wavefront, RMS : λ/2

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant