

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25.4 X 177.8mm EFL 90° Protected Silver 100A Off-Axis Parabolic Mirror



Stock #36-592 3-4 DAYS

[Other Coating Options](#)



1



€490,00

ADD TO CART

Qty 1-5

€490,00

Qty 6+

€441,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:  
Off-Axis Parabolic Mirror

Diameter (mm):  
25.40 +0.00/-0.38

Effective Focal Length EFL (mm):

|                                                                                                                              |
|------------------------------------------------------------------------------------------------------------------------------|
| 177.80                                                                                                                       |
| <b>Focal Length Tolerance (%):</b><br>±1                                                                                     |
| <b>Radius of Curvature (mm):</b><br>177.80                                                                                   |
| <b>Coating:</b><br>Protected Silver (450-12000nm)                                                                            |
| <b>Coating Type:</b><br>Metal                                                                                                |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≥98% @ 2,000 - 12,000nm,<br>R <sub>avg</sub> (typical) 96% @ 450 - 2,000nm |
| <b>Off-Set Angle (°):</b><br>90                                                                                              |
| <b>Parent Focal Length PFL (mm):</b><br>88.9                                                                                 |
| <b>Surface Figure, RMS:</b><br>λ/4                                                                                           |
| <b>Surface Roughness (Angstroms):</b><br><100 RMS                                                                            |
| <b>Wavelength Range (nm):</b><br>450 - 12000                                                                                 |
| <b>Clear Aperture (%):</b><br>90                                                                                             |
| <b>Surface Quality:</b><br>80-50                                                                                             |
| <b>Compatible Mounting Plates:</b><br><a href="#">#47-111</a>                                                                |
| <b>Substrate:</b><br>Aluminum 6061-T6                                                                                        |
| <b>Y Offset (mm):</b><br>177.8                                                                                               |
| <b>Reflected Wavefront, RMS:</b><br>λ/2                                                                                      |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |