

25.4mm, ISP Optics Calcium Fluoride Equilateral Prism | CF-EP-25

See More by [ISP Optics](#)



Stock #19-710 3-4 DAYS

- 1 + **€1.700,00**

ADD TO CART

Qty 1-5
€1.700,00

Qty 6+
€1.360,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating: Uncoated
Substrate: ☐ Calcium Fluoride (CaF ₂)
Surface Quality:

40-20
Type: Equilateral Prism
Dimensional Tolerance (mm): ±0.25
Angle Tolerance (arcmin): ±10
Clear Aperture (%): 85
Length of Hypotenuse (mm): 25.40
Length of Legs (mm): 25.40
Wavelength Range (nm): 200 - 7000
Wavelength Range (µm): 0.2 - 7
Surface Flatness (P-V): 2λ
Model Number: CF-EP-25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View