

25.4mm Clear Aperture, 5 Arcsec, Aluminum Retroreflector



Stock #46-174 3-4 DAYS

⊖ 1 ⊕

€760,00

ADD TO CART

Qty 1+
€760,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Beam Deviation (arcsec):
5.00

Clear Aperture CA (mm):
25.4

Coating:
Enhanced Aluminum (450-650nm)

Diameter (mm):
41.30

Exiting Wavefront Accuracy:
0.6λ

Substrate: 

Surface Quality:
80-50

Mounting Threads:
(2) ¼-20, M6 x 1.0

Type:
Retroreflector

Dimensional Tolerance (mm):
±1.6

Image Orientation:
Left-Handed

Ray Deviation (°):
180

Wavelength Range (nm):
400 - 700

Regulatory Compliance

RoHS 2015:
Compliant

REACH 201:
Compliant

Certificate of Conformance:
[View](#)