

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC X/10 Laser Line Coated Windows

Stock #38-979 CLEARANCE 3-4 DAYS



1



€109,95

ADD TO CART

Qty 1+

€109,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):

0

Clear Aperture CA (mm):

22.86

Coating:

Laser V-Coat (1064nm)

Design Wavelength DWL (nm):

1064

Diameter (mm): 25.40 +0.00/-0.10
Substrate: N-BK7
Index of Refraction n_d: 1.516
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Type: Laser Line Window
Parallelism (arcmin): <3
Bevel: Protective as needed
Clear Aperture (%): 90
Abbe Number (v_d): 64.17
Coating Specification: R_{abs} <0.25% @ 1064nm
Surface Flatness (P-V): λ/10
Damage Threshold, By Design: 15 J/cm² @ 1064nm, 20ns, 20Hz
Edges: Fine Ground

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View