

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

25.4mm Dia, 1200-1650nm, $\lambda/2$ Achromatic waveplate



Achromatic Waveplates (Retarders)

Stock #46-563 3-4 DAYS



1



€870,00

ADD TO CART

Qty 1-5

€870,00

Qty 6+

€755,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
11.5

Coating:
R_{avg} <0.5% @ 1200 - 1650nm

Diameter (mm):
25.40

Substrate: ☐ Crystal Quartz and MgF ₂
Retardance: λ/2
Surface Quality: 20-10
Thickness (mm): 9.00 ±0.1
Type: Achromatic Waveplate
Parallelism (arcmin): <1
Dimensional Tolerance (mm): +0/-0.25
Construction: Crystalline
Transmitted Wavefront, P-V: λ/4 @ 633nm
Housing Tolerance (mm): +0/-0.25
Retardance Tolerance: ≤ λ/100
Temperature Coefficient (λ/°C): <1/500
Coating Specification: R _{avg} <0.5% @ 1200 - 1650nm
Wavelength Range (nm): 1200 - 1650
Damage Threshold, By Design: ☐ 500 kW/cm ²
Configuration: Air Spaced

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View