

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Ultrafast Harmonic Separators

Stock #22-678 3-4 DAYS



1



€245,00

ADD TO CART

Qty 1-5

€245,00

Qty 6+

€205,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):

0

Clear Aperture (%):

>85

Coating Specification:

Surface 1: R_{avg} >99% @ 376 - 425nm T_{avg} >98% @

700 - 900nm Surface 2: R _{avg} <1% @ 700 - 900nm
Construction: Dichroic
Diameter (mm): 25.40 +0.00/-0.10
Parallelism (arcmin): <3
Reflection Wavelength (nm): 400
Substrate: ☐ Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/8
Surface Quality: 10-5
Thickness (mm): 3.00 ±0.10
Transmission Wavelength (nm): 800
Type: Harmonic Beamsplitter
GDD Specification: Surface 1: 0±20fs ² @ 376 - 425nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View