

## 25.4mm Dia f/0.5 Uncoated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock **#33-257** 3-4 DAYS

- 1 +

€60,00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| €60,00                        |
| Qty 11+                       |
| €50,00                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

### Get Product Downloads

**Diameter (mm):**  
25.40 ±0.1

**Effective Focal Length EFL (mm):**  
12.70 @ 632.8nm

|                                                                                                             |
|-------------------------------------------------------------------------------------------------------------|
| <b>Numerical Aperture NA:</b><br>1.00                                                                       |
| <b>Back Focal Length BFL (mm):</b><br>8.00                                                                  |
| <b>Substrate:</b> <br>PMMA |
| <b>Focal Length Tolerance (%):</b><br>±1                                                                    |
| <b>Aspheric Design Wavelength (nm):</b><br>632.8                                                            |
| <b>Coating:</b><br>Uncoated                                                                                 |
| <b>Clear Aperture CA (mm):</b><br>23.9                                                                      |
| <b>Edge Thickness ET (mm):</b><br>4.00                                                                      |
| <b>Center Thickness CT (mm):</b><br>13.67                                                                   |
| <b>f/#:</b><br>0.5                                                                                          |
| <b>Bevel:</b><br>Protective bevel as needed                                                                 |
| <b>Operating Temperature (°C):</b><br>80.00                                                                 |
| <b>Radius R (mm):</b><br>74.68                                                                              |
| <b>Type:</b><br>Aspheric Lens                                                                               |
| <b>Wavelength Range (nm):</b><br>400 - 1100                                                                 |
| <b>Conjugate Distance:</b><br>Infinite                                                                      |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 224:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |