


TECHSPEC®

25.4mm Dia. Laser Mirror Substrate



TECHSPEC® Laser Mirror Substrates

Stock **#37-685** 3-4 DAYS



1



€95,00

ADD TO CART

Qty 1-10

€95,00

Qty 11+

€84,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror Substrate

Parallelism (arcmin):
<3

Clear Aperture (%) : 90
Back Surface: Commercial Polish
Surface Flatness (P-V): λ/10
Coating: Uncoated
Diameter (mm): 25.40 +0.00/-0.10
Thickness (mm): 6.35 ±0.20
Substrate: Fused Silica (Corning 7980)

Regulatory Compliance

Reach 191: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View