


In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

254mm Dia. X 1mm High Efficiency window



Stock #63-220 ☐ In Stock



1



€87,50

ADD TO CART

Qty 1-5

€87,50

Qty 6+

€70,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Bevel:
Protective as needed

Clear Aperture (%):
≥90

Clear Aperture CA (mm): 228.60
Diameter (mm): 254.00 ±0.76
Thickness (mm): 1.00 ±0.25
Coating: BBAR (425-700nm)
Coating Specification: R _{avg} ≤0.5% @ 425 - 700nm
Edges: Ground
Substrate: Float Glass
Surface Quality: 80-50
Transmission (%): 96.9 Average (typical)
Type: Protective Window
Wavelength Range (nm): 425 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant