

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 25.4mm Dia., 2.3mm Thick, VIS-NIR AR Coated Sapphire window



Stock **#39-248** 3-4 DAYS

- 1 + **€120,50**

ADD TO CART

Qty 1-24

€120,50

Qty 25+

€96,50

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
72.24

Axis Orientation:
Random

Bevel:
Protective as needed

Birefringence (n_o-n_e): 0.008 for Visible Light Orthogonal to Optical Axis
Clear Aperture (%) : ≥90
Clear Aperture CA (mm) : 22.86
Diameter (mm) : 25.40 ±0.05
Thickness (mm) : 2.30 ±0.10
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{avg} ≤0.25% @880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C) : 8.8
Density (g/cm³) : 3.97
Edges : Fine Ground
Index of Refraction n_d : 1.77
Knoop Hardness (kg/mm²) : 1900
Parallelism (arcmin) : ≤3.5
Poisson's Ratio : 0.27
Substrate : Sapphire (Al ₂ O ₃)
Surface Flatness (P-V) : 2λ (typical)
Surface Quality : 80-50
Type : Protective Window
Wavelength Range (nm) : 400 - 1000
Young's Modulus (GPa) : 435

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant