

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #36-212 3-4 DAYS



1



€88,00

ADD TO CART

Qty 1-5

€88,00

Qty 6+

€70,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
50.00

Substrate:
[N-BK7](#)

f/#:
1.96850393700787

Numerical Aperture NA: 0.25
Coating: VIS 0° (425-675nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): 46.93
Center Thickness CT (mm): 4.65
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.4 x 25.4
Edge Thickness ET (mm): 1.31
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 25.84
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant