

TECHSPEC[®] 25.4mm Kinematic Mount



25.4mm Kinematic Mount, #85-695

Stock **#85-695** 11 In Stock

-

1

+

€196⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€196,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Tip-Tilt	Function:
Circular	Type of Optics:

Accepts 25/25.4mm Diameter Optics		Note:
Physical & Mechanical Properties		
30.0	Compatible Plate Inner Diameter (mm):	
25.4	Inner Diameter (mm):	
Black Anodized Aluminum	Construction:	
12.7	Through Hole Diameter (mm):	
30 Dia.	Dimensions (mm):	
0.5	Adjustment Screw Pitch (mm):	
±8 Tip/Tilt	Travel (°):	
Threading & Mounting		
25.0 - 25.4	Size of Compatible Optics (mm):	
Regulatory Compliance		
Compliant	RoHS 2015:	
View	Certificate of Conformance:	
Compliant	Reach 235:	

PRODUCT DETAILS

- Available for a Range of Optical Components
- Anodized Aluminum Construction with Stainless Steel Screws
- 0.5mm Pitch Fine Adjustment Screw
- [Fixed Optical Mounts](#) Also Available

Ideal for beam steering applications, TECHSPEC® Cage System Adjustable Optical Mounts are used to integrate a variety of optical components into a TECHSPEC Cage System. Designed to fit within the inner diameter of 25mm or 30mm standard [cage system plates](#), these optical mounts utilize set screws to secure optical components in place, providing the stability and adjustment needed for precision optical alignment. [#85-695](#) 25.4mm Kinematic Mount features a 12.7mm clear aperture and can be paired with [#85-699](#) 45° plate beamsplitter mount.