

## 25/25.4mm, Mounting Cell



25.4mm, Mounting Cell, #56-760

Stock #56-760 **20+ In Stock**

⊖ 1 ⊕ €27<sup>25</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-9	€27,25 each
Qty 10-25	€24,60 each
Qty 26-49	€23,40 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Fixed **Type:**

Circular **Type of Optics:**

### Physical & Mechanical Properties

**Construction:**

Black Anodized Aluminum

**Max. Thickness of Compatible Optics (mm):**  
3.2

**Cell Diameter (mm):**  
30.0

### Threading & Mounting

**Size of Compatible Optics (mm):**  
25.0 - 25.4

**Cell Thickness (mm):**  
5.0

### Regulatory Compliance

**RoHS 2015:**  
[Exempt](#)

**Certificate of Conformance:**  
[View](#)

**Reach 247:**  
[Contains SVHC\(s\)](#)

## Product Details

- Allows Stacking of 3 or 5 Filters
- Black Anodized Aluminum
- [Posts](#) and [Post Holders](#) Required for Mounting

Fixed/Multiple Filter Mounts are ideal for use with neutral density filters in stacking applications. Mounting cell holds filter with diameter "F" in place with a retainer ring. Mounting cell sits securely in filter holder. Fixed/Multiple Filter Mounts can also hold unmounted filters with diameter "A". A filter holder and filter cell are required for a complete stacking system, such as the one illustrated in the product image. These mounts are constructed of black anodized aluminum and are optimal for mounting 3 or 5 circular optics.

[Posts](#) and [Post Holders](#) are required for mounting to a breadboard.

## Technical Information

Stock No.	A	B	C	D	No. of Slots	No. of Cell Slots
<a href="#">#55-006</a>	30mm	50mm	34mm	5mm	4	3
<a href="#">#55-007</a>	50mm	70mm	44mm	5mm	5	5

Stock No.	F	G	H
<a href="#">#56-759</a>	12.7mm	10.2mm	30mm
<a href="#">#55-008</a>	25mm	22.5mm	30mm
<a href="#">#56-760</a>	25.4mm	22.9mm	30mm
<a href="#">#55-009</a>	50mm	47mm	52mm