

25.0/25.4mm Optic Dia., 5 Axes Optical Mount



5 Axes Optical Mount



Stock **#13-776** [CONTACT US](#)

-

1

+

€755^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	€755,00 each
Qty 5-9	€717,60 each
Qty 10+	€642,10 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Adjustable - Linear (XYZ) & Tip-Tilt

Type of Optics:

Circular

Physical & Mechanical Properties	
22.0	Clear Aperture CA (mm):
±2.0 in X and Y, ±1.5 in Z	Travel (mm):
0.3	Weight (kg):
Black Anodized Aluminum	Construction:
±2	Tip/Tilt Angle (°):

Threading & Mounting	
25.0 - 25.4	Size of Compatible Optics (mm):
12.5 (Max)	Thickness of Compatible Optics (mm):
M6 x 1.0	Compatible Post:

Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

Product Details

- 2-Axis, 3-Axis, and 5-Axis Adjustable Mounts Available
- Options for 12.5mm (0.5"), 25mm (1"), and 50mm (2") Dia. Optics
- M6 Mounting Threads

Multi-Axis Adjustable Optic Mounts can adjust optic positioning along the X- and Y-axes, as well as through optional Z-axis and Tip/Tilt adjustment. Compact packaging allows for fine alignment adjustments without the additional use of bulkier stages. Multi-Axis Adjustable Optic Mounts are ideal for alignment adjustments in prototyping and precision laboratory benchtop optical systems. These mounts include M6 mounting threads making them compatible with our standard [Metric Stainless Steel Mounting Posts](#). A retainer ring and Delrin ring are used together to secure the optic without damaging its surface.

Technical Information

