

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 25.4mm Silver and VIS 0° Coated, Corner Cube Prism



N-BK7 Corner Cube Retroreflectors with Black Overpaint

Stock #48-607 3-4 DAYS



1



€300,00

ADD TO CART

Qty 1-5

€300,00

Qty 6+

€240,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcsec):

3

Coating:

S1 Silver with protective overcoat (black overpaint) &
S2 VIS 0°

Diameter (mm):

25.40 +0.0/-0.1
Substrate: N-BK7
Height (mm): 19.05
Surface Quality: 60-40
Type: Retroreflector
Bevel: Protective bevel as needed
Clear Aperture (%) : 95
Height Tolerance (mm): ±0.25
Image Orientation: Left-Handed
Note: Black Overpaint is 30-60µm Thick
Coating Specification: Reflective Surfaces: R _{abs} > 97% FROM400 - 2500nm @0° AOI R _{avg} > 98% FROM400 - 2500nm @0° AOI Entrance:R _{avg} ≤0.4% @425 - 675nm
Ray Deviation (°): 180
Wavelength Range (nm): 425 - 675
Surface Flatness (P-V): λ/8
Damage Threshold, By Design: View Entrance: 0.5 J/cm² @ 532nm & 1064nm, 10ns Reflective Surfaces: 5 J/cm2 @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View