

25.4mm Travel, Metric Micrometer, Solid Top 127.0mm Stage



Stock **#55-463** [CONTACT US](#)

- 1 + **€1.223,00**

ADD TO CART

Qty 1+
€1.223,00

Volume Pricing
Request Quote

i Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement: Linear (X)
Guide System: Ball Bearing
Type of Drive: Digital Micrometer (Metric)
Drive Orientation: Center Drive
Type: Metric

Stage Size (mm): 127 x 127
Travel (mm): 25
Construction: Aluminum Top and Base/440C Stainless Steel Bearings
Graduation (mm): 0.001
Load Capacity, Normal (kg): 48
Load Capacity, T_a (kg): 13.6
Load Capacity, T_b (kg): 0.9
Note: Solid Top
Stage Size (inches): 5.00 x 5.00
Straight Line Accuracy (μm): 2 per 25 mm of travel
Weight (g): 1400

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View