

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

25.4mm Travel, Metric Micrometer, Thru-Hole 66.5mm Stage



Stock #55-464 3-4 DAYS



1



€1.193,00

ADD TO CART

Qty 1+

€1.193,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
Digital Micrometer (Metric)

Drive Orientation:
Center Drive

Type:
Metric

Stage Size (mm): 66.5 x 66.5
Travel (mm): 25
Construction: Aluminum Top and Base/440C Stainless Steel Bearings
Graduation (mm): 0.001
Load Capacity, Normal (kg): 28
Load Capacity, T_a (kg): 4.5
Load Capacity, T_b (kg): 0.9
Note: Thru-Hole
Stage Size (inches): 2.62 x 2.62
Straight Line Accuracy (μm): 2 per 25 mm of travel
Weight (g): 630

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View