

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC® Beam Shaping PCV Cylinder Lenses

Stock #34-622 3-4 DAYS



1



€95,00

ADD TO CART

Qty 1-5

€95,00

Qty 6+

€76,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):

25.40 +0.0/-0.025

Effective Focal Length EFL (mm):

-50.00

Substrate:

[N-BK7](#)

f/#: 2
Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -51.98
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 22.86
Edge Thickness ET (mm): 6.23
Radius R₁ (mm): 25.84
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <5
Power Axis Wedge (arcmin): <5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View