

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #19-714 3-4 DAYS



1



€2.265,00

ADD TO CART

Qty 1-5

€2.265,00

Qty 6+

€1.812,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
Uncoated

Substrate: ☐
Zinc Selenide (ZnSe)

Surface Quality:

60-40
Type: Equilateral Prism
Dimensional Tolerance (mm): ±0.25
Angle Tolerance (arcmin): ±10
Clear Aperture (%): 85
Length of Hypotenuse (mm): 25.40
Length of Legs (mm): 25.40
Wavelength Range (nm): 600 - 18000
Wavelength Range (µm): 0.6 - 18
Surface Flatness (P-V): 2λ
Model Number: GE-EP-25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View