

25° Diffusing Angle 25mm Dia Mounted



Stock #54-498 CLEARANCE 3-4 DAYS

- 1 + **€180,00**

ADD TO CART

Qty 1-5
€180,00

Qty 6+
€153,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle Tolerance (°): ±2.5
Diffusing Angle (°): 25 (FWHM)
Clear Aperture CA (mm): 21.6
Diameter (mm):

25.00 ±0.1
Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 2.60
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Construction: Mounted
Damage Threshold, By Design: ☐ 0.22 J/cm ² @ 1064nm, 10ns (typical)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant