

TECHSPEC®

25mm Dia., UV Enhanced Aluminum, $\lambda/10$ Stemmed Mirror



TECHSPEC® Stemmed Mirror



Stock **#14-580** 3-4 DAYS

- 1 +

€132,00

ADD TO CART

Qty 1-5
€132,00
Qty 6+
€105,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Surface Flatness (P-V):

N/10

Substrate: [Fused Silica](#) (Coming 7980)

Back Surface:
Commercial Polish

Surface Quality:
20-10

Coating Specification:
R_{avg} >89% @ 250 - 450nm
R_{avg} >85% @ 250 - 700nm

Coating:
Enhanced Aluminum (250-700nm)

Coating Type:
Metal

Clear Aperture (%):
90.00

Edges:
Ground, protective bevel as needed

Thickness (mm):
13.00 ±0.20

Type:
Stemmed Mirror

Wavelength Range (nm):
250 - 700

Compatible Kinematic Mount:
[#58-853](#)

Stem Diameter (mm):
12.50 +0.00/-0.10

Stem Length (mm):
6.50 ±0.20

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)