

TECHSPEC[®] 25mm Cage 12.7mm Diameter Lens Mount



#85-545



Stock #85-547 1 In Stock

-

1

+

€45^{.75}

ADD TO CART

Volume Pricing	
Qty 1+	€45,75 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Fixed	Function:
Circular	Type of Optics:
Fixed	Type:

Physical & Mechanical Properties	
Compatible Plate Inner Diameter (mm):	25.0
Length (mm):	10.00
Clear Aperture CA (mm):	11.00
Construction:	Black Anodized Aluminum
Dimensions (mm):	25 Dia.

Threading & Mounting	
Size of Compatible Optics (mm):	12.7
Thickness of Compatible Optics (mm):	1.9 - 5.0
Thread Type:	M23.2 x 0.75

Regulatory Compliance	
RoHS 2015:	Compliant
Certificate of Conformance:	View
REACH 241:	Compliant

Product Details

- Available for a Range of Optical Lens Diameters
- Adds Additional Adaptability to Cage System
- Retaining Ring Included

TECHSPEC® Cage System Optical Lens Mounts, constructed of anodized aluminum, are designed to be used in a two-step process. First, secure the optical component within the lens mount using the included retaining ring. Second, secure the lens mount within the inner diameter of a [cage system plate](#). By enabling the addition and removal of lens mounts from plates, the system creates a wide range of flexibility for cage setups. TECHSPEC Cage System Optical Lens Mounts are ideal as stand-alone components or combined with [cage system tubes](#).

Note: [#85-678](#) is a two-piece assembly that can be used with either 25mm or 30mm cage system plates. Replacement retaining rings are sold separately.