

TECHSPEC® 25mm Cage 12.7mm Diameter Thick Lens Mount



#85-545



Stock #85-548 **3 In Stock**

⊖ 1 ⊕ €45⁷⁵

ADD TO CART

Volume Pricing	
Qty 1+	€45,75 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Fixed	Function:
Circular	Type of Optics:
Fixed	Type:

Physical & Mechanical Properties

Compatible Plate Inner Diameter (mm):

25.0

Length (mm):

15.00

Clear Aperture CA (mm):

11.00

Construction:

Black Anodized Aluminum

Dimensions (mm):

25 Dia.

Threading & Mounting

Size of Compatible Optics (mm):

12.7

Thickness of Compatible Optics (mm):

1.9 - 10.0

Thread Type:

M23.2 x 0.75

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

REACH 241:

[Compliant](#)

Product Details

- Available for a Range of Optical Lens Diameters
- Adds Additional Adaptability to Cage System
- Retaining Ring Included

TECHSPEC® Cage System Optical Lens Mounts, constructed of anodized aluminum, are designed to be used in a two-step process. First, secure the optical component within the lens mount using the included retaining ring. Second, secure the lens mount within the inner diameter of a [cage system plate](#). By enabling the addition and removal of lens mounts from plates, the system creates a wide range of flexibility for cage setups. TECHSPEC Cage System Optical Lens Mounts are ideal as stand-alone components or combined with [cage system tubes](#).

Note: [#85-678](#) is a two-piece assembly that can be used with either 25mm or 30mm cage system plates. Replacement retaining rings are sold separately.