

TECHSPEC® 25mm Dia., UV Enhanced Aluminum, $\lambda/10$ Stemmed Mirror



TECHSPEC® Stemmed Mirror



Stock **#14-580** CLEARANCE 3-4 DAYS

- 1 +

€132,00

ADD TO CART

Qty 1-5
€132,00
Qty 6+
€105,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Surface Flatness (P-V):

N10
Substrate: Fused Silica (Coming 7980)
Back Surface: Commercial Polish
Surface Quality: 20-10
Coating Specification: R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Clear Aperture (%): 90.00
Edges: Ground, protective bevel as needed
Thickness (mm): 13.00 ±0.20
Type: Stemmed Mirror
Wavelength Range (nm): 250 - 700
Compatible Kinematic Mount: #58-853
Stem Diameter (mm): 12.50 +0.00/-0.10
Stem Length (mm): 6.50 ±0.20

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View