

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 25mm Dia X 100mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #46-018 3-4 DAYS

1 €70,00

ADD TO CART

Qty 1-5

€70,00

Qty 6+

€56,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Effective Focal Length EFL (mm):
100.00

Substrate: ☐
N-BK7

f/#: 4
Numerical Aperture NA: 0.13
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 97.98
Center Thickness CT (mm): 3.16
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.63
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 51.85
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View