

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #89-362 3-4 DAYS

[Other Coating Options](#)



1



€782,00

ADD TO CART

Qty 1-5

€782,00

Qty 6+

€625,60

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.10

Effective Focal Length EFL (mm):
12.50 @ 4000nm

Numerical Aperture NA:
1.00

Back Focal Length BFL (mm): 10.70
Substrate: Silicon (Si)
Aspheric Design Wavelength (nm): 4000
Asphere Figure Error, RMS @ 632.8nm: λ/6
Coating: BBAR (3000-5000nm)
Coating Specification: R _{avg} <3% @ 3 - 5μm
Surface Accuracy, P-V (μm): <0.3
Centering (arcmin): ≤10
Centering, ETD (μm): <21.8
Surface Quality: 60-40
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 2.37
Center Thickness CT (mm): 4.75 ±0.10
f#: 0.5
Bevel: Protective bevel as needed
Edges: Diamond Turned
Radius R ₂ (mm): 87.361
Shape of Back Surface: Concave
Type: Aspheric Lens
Wavelength Range (nm): 3000 - 5000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant