

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25mm Dia. X 150mm FL, VIS-NIR, Inked, Double-Convex Lens



Stock #45-894-INK [CONTACT US](#)

- 1 + €60,00

ADD TO CART

Qty 1-9

€60,00

Qty 10+

€54,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Back Focal Length BFL (mm):
148.88

Effective Focal Length EFL (mm): 150.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870 nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.40
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.39
Radius R₁=R₂ (mm): 154.52
Clear Aperture CA (mm): 24.00
f/#: 6.00
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.08
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View