

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #21-096 3-4 DAYS

[Other Coating Options](#)



1



€235,00

ADD TO CART

Qty 1-5

€235,00

Qty 6+

€199,80

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):  
250.00 @ 10.6µm

Back Focal Length BFL (mm):

|                                                                                                               |
|---------------------------------------------------------------------------------------------------------------|
| 249.12                                                                                                        |
| <b>Coating:</b><br>BBAR (1650-3000nm)                                                                         |
| <b>Coating Specification:</b><br>R <sub>avg</sub> <1% @ 1650 - 3000nm<br>R <sub>abs</sub> <2% @ 1650 - 3000nm |
| <b>Substrate:</b> <input type="checkbox"/><br>Silicon (Si)                                                    |
| <b>Surface Quality:</b><br>60-40                                                                              |
| <b>Power (P-V) @ 632.8nm:</b><br>2λ                                                                           |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/2                                                                   |
| <b>Centering (arcmin):</b><br><3                                                                              |
| <b>Center Thickness CT (mm):</b><br>3.00 ±0.10                                                                |
| <b>Edge Thickness ET (mm):</b><br>2.87                                                                        |
| <b>Radius R<sub>1</sub> (mm):</b><br>604.40                                                                   |
| <b>Clear Aperture CA (mm):</b><br>24                                                                          |
| <b>f/#:</b><br>10.00                                                                                          |
| <b>Numerical Aperture NA:</b><br>0.05                                                                         |
| <b>Type:</b><br>Plano-Convex Lens                                                                             |
| <b>Bevel:</b><br>Protective bevel as needed                                                                   |
| <b>Wavelength Range (nm):</b><br>1650 - 3000                                                                  |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |