

TECHSPEC® 25mm Dia. x 25mm FL, Uncoated Germanium Meniscus Lens



Stock **#87-955** 3-4 DAYS

- 1 + **€400,00**

ADD TO CART

Qty 1-5
€400,00
Qty 6+
€320,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
25.00

Substrate: ☐
Germanium (Ge)

f/#:

1.00
Numerical Aperture NA: 0.50
Coating: Uncoated
Type: Meniscus Lens
Wavelength Range (nm): 2000 - 14000
Back Focal Length BFL (mm): 23.34
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <3
Clear Aperture (%): 90.00
Edge Thickness ET (mm): 1.3
Focal Length Specification Wavelength (μm): 10.6
Radius R₁ (mm): 28.32
Radius R₂ (mm): 42.46
Surface Quality: 60-40
Wavelength Range (μm): 2 - 14

Regulatory Compliance

RoHS: Compliant
Reach 224: Compliant
Certificate of Conformance: View