

TECHSPEC® 25mm Dia. x 30mm FL, 8-12µm Coated Germanium Meniscus Lens



Stock #87-968 CONTACT US

1 €519,00

ADD TO CART

|         |
|---------|
| Qty 1-5 |
| €519,00 |

|         |
|---------|
| Qty 6+  |
| €415,20 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):  
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):  
30.00

Substrate: ☐  
Germanium (Ge)

f/#:

|                                                                    |
|--------------------------------------------------------------------|
| 1.2                                                                |
| <b>Numerical Aperture NA:</b><br>0.42                              |
| <b>Coating:</b><br>BBAR (8000-12000nm)                             |
| <b>Type:</b><br>Meniscus Lens                                      |
| <b>Wavelength Range (nm):</b><br>8000 - 12000                      |
| <b>Back Focal Length BFL (mm):</b><br>28.31                        |
| <b>Center Thickness CT (mm):</b><br>2.50                           |
| <b>Center Thickness Tolerance (mm):</b><br>±0.10                   |
| <b>Centering (arcmin):</b><br><3                                   |
| <b>Clear Aperture (%):</b><br>90.00                                |
| <b>Coating Specification:</b><br>R <sub>avg</sub> <3.0% @ 8 - 12µm |
| <b>Edge Thickness ET (mm):</b><br>1.5                              |
| <b>Focal Length Specification Wavelength (µm):</b><br>10.6         |
| <b>Radius R<sub>1</sub> (mm):</b><br>33.38                         |
| <b>Radius R<sub>2</sub> (mm):</b><br>50.04                         |
| <b>Surface Quality:</b><br>60-40                                   |
| <b>Wavelength Range (µm):</b><br>8 - 12                            |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |